



Main

| | |
|------------------------------|------------------------|
| Product or Component Type | Dry Sealed Transformer |
| Primary to Secondary Voltage | 120 x 240 V 120/240 V |
| Full Capacity Taps | 0 |

Complementary

| | |
|--------------------|----------------------|
| Enclosure Code | 13B |
| Phase | 1 phase |
| Power Rating | 10 kVA |
| Temperature rise | 115 °C |
| Height | 14.75 in (374.65 mm) |
| Width | 9.75 in (247.65 mm) |
| Depth | 11.75 in (298.45 mm) |
| Enclosure mounting | Wall mounted |
| Enclosure Material | Painted sheet steel |

Environment

| | |
|------------------------|---------------------------|
| Enclosure Type | NEMA 3R |
| Insulation temperature | 356 °F (180 °C) |
| Product Certifications | UL Listed CULus CSA |

Ordering and shipping details

| | |
|-----------------------|---------------------------|
| Category | 16277-RESIN LVGP XFMR |
| Discount Schedule | PE2 |
| GTIN | 785901555537 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 165.00 lb(US) (74.843 kg) |
| Returnability | No |
| Country of origin | US |

Packing Units

| | |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 11.22 in (28.499 cm) |
| Package 1 width | 10.24 in (26.01 cm) |
| Package 1 Length | 13.23 in (33.604 cm) |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| PVC free | Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|