

# Product data sheet

## Characteristics

# 10S67F

Low voltage transformer, encapsulated dry type, 1 phase, 10kVA, multiple voltages, Type 3R



### Main

Product or Component Type	Dry Sealed Transformer
Primary to Secondary Voltage	190/200/208/220 x 380/400/416/440 V 110/220 V
Full Capacity Taps	0

### Complementary

Enclosure Code	13B
Phase	1 phase
Power Rating	10 kVA
Temperature rise	115 °C
Height	14.75 in (374.65 mm)
Width	9.75 in (247.65 mm)
Depth	11.75 in (298.45 mm)
Enclosure mounting	Wall mounted
Enclosure Material	Painted sheet steel

### Environment

Insulation temperature	356 °F (180 °C)
Product Certifications	CSA UL Listed CULus TÜV

### Ordering and shipping details

Category	16277-RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	785901069508
Nbr. of units in pkg.	1
Package weight(Lbs)	165.00 lb(US) (74.843 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	15.00 in (38.1 cm)
Package 1 width	12.00 in (30.48 cm)
Package 1 Length	10.00 in (25.4 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------