

# Product data sheet

## Characteristics

# HCM64TS

Trim, I-Line PNLBRD, hcm, surface, 4 pcs, 32x64x8.25 in



### Main

Range	I-Line
Product or Component Type	Trim
Parts Quantity	4

### Complementary

Width	32.25 in (819.15 mm)
Height	64 in (1625.60 mm)
Product Destination	Panelboard HCM 32 in (812.80 mm) 64 in (1625.60 mm) 8.25 in (209.55 mm)
Device Mounting	Surface
Net Weight	31.00 lb(US) (14.06 kg)

### Environment

Standards	CE cULus
-----------	-------------

### Ordering and shipping details

Category	00112-I-LINE PB RTA TRIMS
Discount Schedule	PE1A
GTIN	785901089094
Nbr. of units in pkg.	1
Package weight(Lbs)	27.50 lb(US) (12.474 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.20 in (5.6 cm)
Package 1 width	15.98 in (40.6 cm)
Package 1 Length	47.72 in (121.2 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------