

# Product data sheet

## Characteristics

# 1.5S7F

Low voltage transformer, encapsulated dry type, 1 phase, 1.5kVA, 208V primary, 120/240V secondary, Type 3R

### Main

Product or Component Type	Dry Sealed Transformer
Primary to Secondary Voltage	208 V 120/240 V
Full Capacity Taps	0

### Complementary

Enclosure Code	8A
Phase	1 phase
Power Rating	1.5 kVA
Temperature rise	115 °C
Height	8.25 in (209.55 mm)
Width	8.68 in (220.47 mm)
Depth	6.56 in (166.62 mm)
Enclosure mounting	Wall mounted
Enclosure Material	Painted sheet steel

### Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product Certifications	CSA CULus UL Listed

### Ordering and shipping details

Category	16277-RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	785901313212
Nbr. of units in pkg.	1
Package weight(Lbs)	30.1 lb(US) (13.65 kg)
Returnability	No
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------