

Product data sheet

Characteristics

HCM73TSVD

Trim, I-Line PNLBRD, hcm, surface, 4 pcs, w/ door, vent, 32x73x8.25 in



Main

Range	I-Line
Product or Component Type	Trim
Enclosure Type	Ventilated
Parts Quantity	4

Complementary

Width	32.25 in (819.15 mm)
Height	73 in (1854.20 mm)
Product Destination	Panelboard HCM 32 in (812.80 mm) 73 in (1854.20 mm) 8.25 in (209.55 mm)
Device Mounting	Surface
Number of Door	1

Environment

Standards	CULus CE
-----------	-------------

Ordering and shipping details

Category	00112-I-LINE PB RTA TRIMS
Discount Schedule	PE1A
GTIN	785901949268
Nbr. of units in pkg.	1
Package weight(Lbs)	1 lb(US) (0.45 kg)
Returnability	Yes

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes