

Product data sheet

Characteristics

HCM64TSD

Trim, I-Line PNLBRD, hcm, surface, 4 pcs, w/
door, 32x64x8.25 in



Main

Range	I-Line
Product or Component Type	Trim
Parts Quantity	4

Complementary

Width	32.25 in (819.15 mm)
Height	64 in (1625.60 mm)
Product Destination	Panelboard HCM 32 in (812.80 mm) 64 in (1625.60 mm) 8.25 in (209.55 mm)
Device Mounting	Surface
Number of Door	1
Net Weight	58.00 lb(US) (26.31 kg)

Environment

Standards	CULus CE
-----------	-------------

Ordering and shipping details

Category	00112-I-LINE PB RTA TRIMS
Discount Schedule	PE1A
GTIN	785901089117
Nbr. of units in pkg.	1
Package weight(Lbs)	58.70 lb(US) (26.626 kg)
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.30 in (5.842 cm)
Package 1 width	30.80 in (78.232 cm)
Package 1 Length	39.00 in (99.06 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------