

## Datasheet

# RS Pro 95 Series 5mm Pitch Right Angle PCB Terminal Block with Plug-In Termination, 9 Way

RS Stock No: **874-4907**



### Specifications:

Body Orientation	Right Angle
Colour	Green
Current Rating	15 A (UL), 20 A (IEC)
Depth	8.5 mm
Gender	Male
Material	Nylon 66
Mounting Type	PCB
Number of Contacts	9
Number of Rows	1
Pitch	5 mm
Termination Method	Plug In
Type	PCB Header
Voltage Rating	300 V (UL), 450 V (IEC)
Width	12 mm
Insulation Withstands Voltage	2000 V ac



Operating Temperature Range	-40 to +105°C
Insulation Resistance	500 mΩ
Flammability Rating	UL 94 V-0