

# Han 24B-AK with stainless-steel cord



Part number	09 30 024 5417
Specification	Han 24B-AK with stainless-steel cord
HARTING eCatalogue	https://b2b.harting.com/09300245417

Image is for illustration purposes only. Please refer to product description.

### Identification

Accessories
Han <sup>®</sup> B
Protection cover
for bulkhead mounted housings
for surface mounted housings
Thermoplastic
With fixing cord

### Version

Size	24 B
Locking type	Double locking lever

# **Technical characteristics**

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Page 1 / 2 | Creation date 2024-03-01 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Electric Stiftung & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)
Specifications and approvals	
Approvals	DNV GL
Commercial data	
Packaging size	1
Net weight	29 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140163188
ETIM	EC002314