

20W Wireless Charging Stand for iPhone and AirPods - MagSafe Charging, 3 ft. Cable, White

MODEL NUMBER: U280MS-2N1-WH



Wirelessly charges a MagSafe-compatible iPhone and earbuds simultaneously with a combined output of 20W.

Features

2-in-1 Charging Stand Handles 2 Devices at the Same Time

This 20W dual-charging output stand is designed for smartphones (including iPhones), earbuds (including AirPods) and other devices compatible with magnetic wireless charging. The top charging pad for smartphones extends toward you, so you can scroll, text or watch videos in landscape or portrait mode while the phone is charging. The bottom pad is for AirPods and other wireless charging-compatible earbuds, which can be charged in their case. Both charging pads can be used simultaneously.

Supports Apple MagSafe Technology for a Secure Charge Every Time

Built-in MagSafe technology helps ensure your iPhone and the U280MS-2N1-WH work together for a complete charge whenever you need it. Magnets inside both your phone and the charging pad prevent the iPhone from falling off the charger and being disconnected while charging. The U280MS-2N1-WH delivers up to 15W of power to smartphones and 5W to wireless headphones or earbuds that support Qi wireless charging.

Compact Charging Stand Fits Comfortably on Any Counter, Table or Workspace

The portable U280MS-2N1-WH takes up hardly any space, making it ideal for your bedside table or desktop. The included three-foot (0.9-meter) USB-C charging cable connects the charging stand to a user-provided USB wall charger or power adapter, such as the 9V 2.2A U280-W01-20C1-G (sold separately). Over-current, over-voltage and short circuit protections defend your devices against damage.

Specifications

OVERVIEW	
UPC Code	037332279309
Product Type	Wireless Charging Stand
Charging Form Factor	Pad/Stand
Device Compatibility	Headphones; Phone

Highlights

- MagSafe wireless charging pad charges iPhone 12 and above with up to 15W of power
- Wireless charging pad charges compatible earbuds with up to 5W of power
- Both charging pads can be used simultaneously for a combined charging output of 20W
- Features over-current, over-voltage and short circuit protections to ensure safe charging
- Developed and tested to Apple's MFi standards

System Requirements

- Works with all MagSafe-compatible smartphones, including iPhone 12 and above
- Charging pad only works with devices compatible with wireless charging

Package Includes

- U280MS-2N1-WH 20W Wireless Charging Stand
- USB-C charging cable (M/M), 3 ft. (0.9 m)
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	Wireless
Country/Region	Global
Host Connector	USB C (FEMALE)
INPUT	
Nominal Input Voltage(s) Supported	5V DC; 9V DC
Input Connection Type	USB Type-C
Input Cord Gauge (AWG)	30+24
Input Plug Type	USB-C (FEMALE)
Input Plug Type Details	USB-A to USB-C Cable Included
Input Current	5V/3A, 9V/3A
Bus Powered	No
OUTPUT	
Output Capacity (Watts)	20
Overload Protection	Yes
POWER	
Power Source Type	USB
Power Source	Unit (Included)
Power Consumption (Watts)	20.00
CONNECTIONS	
Side A - Connector 1	USB C (FEMALE)
Side B - Connector 1	WIRELESS CHARGING COIL
Side B - Connector 2	Magnetic Charger
Connector Style	Straight
CHARGING	
Number of Charging Ports	2
Total Charging Amps	4
Total Charging Watts	20
Charging Method	Magnetic Charger; USB; Wireless
Charging Port Type	(2) WIRELESS CHARGING COIL
Charging Ports Details	MagSafe wireless charging pad provides up to 15W to MagSafe compatible smartphones, such as Apple iPhone 12 or above Wireless charging pad provides up to 5W to wireless charging compatible earbuds
Magnetic Charging	Yes
Wireless Charging	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Overcharge Protection	Yes
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
PHYSICAL	
Color	White
Material of Construction	ABS
Cable Jacket Color	White
Connector Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.5mm
Wire Gauge (AWG)	30+24
Charging Station Form Factor	Pad/Stand
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Cable Length (cm)	90
Unit Dimensions (hwd / in.)	5.490 x 3.560 x 4.950
Unit Dimensions (hwd / cm)	13.9 x 9.04 x 12.58
Unit Dimensions (hwd / mm)	139.4 x 90.4 x 125.8
Unit Packaging Type	Box
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	23° to 113°F (-5° to 45°C)
Operating Humidity Range	20% to 90% RH
Storage Humidity Range	45% to 85% RH
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Driver Required	No
Qi Compliant	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	ICES (Canada); MFi
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS3; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.