





Clamp Meter with automatically ranging true mean squared (TRMS) technology for increased accuracy. This product features the following:

- Test leads measure AC/DC voltage, resistance, continuity, frequency and capacitance and tests diodes
- CAT IV 600V, CAT III 1000V, Class 2, Double insulation safety rating
- 45MM clamp opening for a wide range of applications
- Unique design with grooved housing for superior grip
- Non-contact voltage tester integrated into the clamp

SPECIFICATIONS	
AC CURRENT	1000A
AC VOLTAGE	1000V
RESISTANCE	40MO
CAPACITANCE	40mF
TEMPERATURE	-C40-C1000/-F40-F1832
JAW OPENING	45 mm
OVERVOLTAGE CATEGORY	CAT II 1000V/CATIII 600V
DIMENSIONS	12.25 in x 5.55 in x 2.48 in (31.12 cm x 14.08 cm x 6.29 cm)
WEIGHT	1.7 lb (773.616 g)
UPC #	810053359518

