

13651-20



660W-600V - linear fluorescent lampholder, medium bi-pin, for T8 lamps, with 20 gauge mounting slots, turn type, , body marked UL and CSA.

DISCONTINUED

Suggested Replacement SKUs: :

ROHS Compliant : Yes

Technical Information

Mechanical Specifications

Contact Type : Turn-Type

Panel Thickness : 20 Ga.
Panel

Product Features

Lamp Base : Medium

Lamp Contacts : Bi-Pin

Lamp Type : T8 Only

Lampholder Type : Linear

Light Type : Fluorescent

UPC Code : 078477314968

Country Of Origin : Mexico

SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.
T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·
FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)
5386- 1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2024 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:
www.leviton.com/international/contacts

© 2024 Leviton Manufacturing Co., Inc.