



 PRODUCT-DETAILS

MPNY-750-9-C

CABLE TIE MTG BASE NAT .75IN RUBBER



General Information

Extended Product Type	MPNY-750-9-C
Product ID	7TAG054850R0004
EAN	5414363126089
Catalog Description	CABLE TIE MTG BASE NAT .75IN RUBBER
Long Description	Cable Tie Mounting Base, Natural Nylon 6.6 for Temperatures up to 70 Degrees Celsius (158 F), Length of 18.79mm (0.74 Inches), Width of 18.79mm (0.74 Inches), Height of 5.08mm (0.20 Inches), Mechanical Strength 40 Newtons (9 Pounds), Hole Size #4, Synthetic Rubber Adhesive Mounting Method, 100 Pack

Ordering

EAN	5414363126089
UPC	728494081526
Country of Origin	United States (US)
Selling Unit of Measure	each

Container Information

Package Level 1 Units	100 EA
Package Level 1 Width	127 mm 5 in
Package Level 1 Height	12.7 mm 0.5 in
Package Level 1 Depth / Length	228.6 mm 9 in
Package Level 2 Units	10000 EA
Package Level 2 Width	307.34 mm 12.1 in
Package Level 2 Height	251.46 mm 9.9 in
Package Level 2 Depth / Length	513.08 mm 20.2 in
Package Level 3 Units	350000 EA
Package Level 3 Width	0.025 mm 0.001 in
Package Level 3 Height	0.025 mm 0.001 in
Package Level 3 Depth / Length	0.025 mm 0.001 in

Additional Information

Brand / Label	Catamount
Color	Natural
Effective Date	19960215
Hole Diameter	#4
Material	Nylon/Polyamide 6.6
Mounting Type	Adhesive
Process Temperature Rating	-40 to +185 °F
Product Name	Other
Product Type	Mounting Base

Certificates and Declarations

Data Sheet, Technical Information	MPNY-750-9-C
Declaration of Conformity - CE	9AKK107492A9840

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

