



PRODUCT-DETAILS

# ABB-31E0BB06126

## ABB-31E0BB06126 Low Voltage Dry Type Transformer-SPT



### General Information

Global Commercial Alias	ABB-31E0BB06126
Extended Product Type	ABB-31E0BB06126
Product ID	1TQY200060X0003
Catalog Description	ABB-31E0BB06126 Low Voltage Dry Type Transformer-SPT
Long Description	ABB's Class 2 Control Power Transformer with 1/4" tabs

### Technical

Primary Voltage	120 V AC 240 V AC
Secondary Voltage	24 V AC
Frequency (f)	50/60 Hz
Apparent Power Output	40 V·A
Connection Configuration	Single Phase
Enclosure Type NEMA	Open Type
Transformer Type	Control Power
Housing Material	Core & Coil only
Material of Conductor	Copper
Accessories Available	No

---

### Material Compliance

---

RoHS Status	No declaration needed
REACH Declaration	No declaration needed
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

---



---

### Dimensions

---

Product Net Width	90 mm 3.5 in
Product Net Height	66 mm 2.6 in
Product Net Depth / Length	56 mm 2.2 in

---



---

### Ordering

---

Package Level 1 Units	box 1 piece
-----------------------	-------------

---



---

### Certificates and Declarations

---

Declaration of Conformity - CE	EN60947-4-1:2001
--------------------------------	------------------

---



---

### Installation

---

Instructions and Manuals	No document needed
--------------------------	--------------------

---



---

### Popular Downloads

---

Data Sheet, Technical Information	9AKK107680A9377
-----------------------------------	-----------------

---



---

### Classifications

---

ETIM 8	EC002046 - Power supply transformer
ETIM 9	EC002046 - Voltage measuring transformer
WEEE Category	Product Not in WEEE Scope
WEEE B2C / B2B	Business To Business
UNSPSC	39121026
eClass	V11.0 : 27210901
IDEA Granular Category Code (IGCC)	4169 >> Core & Coil Industrial Control Transformers
Object Classification Code	TA

---

---

## Categories

---

Low Voltage Products and Systems → NEMA Residential and Commercial Portfolio → LV Dry Type Transformers → Small Power Transformers



360