

M22759/11-22

Attributes	Values
No. of Cond.	1
Approx LBS/MFT	4
AWG Size	22
Cond. Material	Silver-Coated Copper
Conductor Stranding	19/34
Insul. Material	Polytetrafluoroethylene (PTFE)
M27500 Component	RC
Max O.D. (in)	0.051
Max. Temp	200C
Mil-Spec	M22759/11
Min O.D. (in)	0.047
Min. Temp	-55C
No. of Strands	19
SAE Spec	AS22759/11
Strand Size	34
Voltage	600