

# 8501RS34V20

Miniature Relay, Harmony 8501R, low voltage, 4PDT, 14 blades, 5A resistive at 240V AC, coil, 0.5HP at 277V AC, 120V AC, 4NO+ 4NC



## Main

Product range	8501R
Product type	Miniature Relay
Relay Type	Low voltage

## Complementary

Mounting type	Socket
Contact composition	4PDT
[Uc] control circuit voltage	120 V AC
Pilot light	No indicator
Manual operator	Without test button
Horsepower rating	Not rated
Breaking capacity	5 A 120 V AC resistive control circuit UL 508 5 A 240 V AC resistive control circuit UL 508 5 A 30 V DC resistive control circuit UL 508
Maximum switching voltage	30 V DC 240 V AC
Contact material	Hermetically sealed silver tin oxide
Operating time	20 ms - pick-up 20 ms - drop-out
Shape of pins	Spade
For use with	8501NR45
Height	1.16 in (29.4 mm)
Width	0.91 in (23.1 mm)
Depth	1.53 in (38.9 mm)

## Environment

Ambient temperature range - operational	-40...131 °F (-40...55 °C)
Product certifications	UL Listed UL Recognized CSA CE

## Ordering and shipping details

Category	21143-8501 R
Discount Schedule	CP2
GTIN	785901031888
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 in (3.302 cm)
Package 1 Width	1.40 in (3.556 cm)
Package 1 Length	2.00 in (5.08 cm)
Package 1 Weight	1.92 oz (54.431 g)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------