



Technical Data Sheet

VA19

*5 in 1 digital
multi-tester*



Application

VA19 is a 5 in 1 digital multi-tester. It combines the functions of Sound Level Meter, Light Meter, Humidity Meter, Temperature Meter and Digital Multimeter in one.

Product Features

Max. Display	3999
Continuity Test	√
Auto Range	√
Data Hold	√
Relative Measurement	√
Back Light	√
Auto Power Off	√
Diode Test	√
Telephone Line Test	-
Network Cable Test	-
Battery Test	-
Power	Battery 6F22(9V)X1
Size	185x85x44 mm (7.28x3.34x1.73 inch)
Weight	~320g (including battery) (11.28 ounces)

Product Specifications

DC Voltage	0.4/4/40/400/600V±0.7%
AC Voltage	4/40/400/600V±0.8%
DC Current	40/400mA/±1.2%,10A±2.0%
AC Current	40/400mA/±1.5%,10A±3.0%
Resistance	400/4K/40K/400K/4MΩ±1.2%,40MΩ±2.0%
Capacitance	4n/40n/400n/4μ/40μF/200μF±5.0%
Frequency	10/100/1K/10K/100KHZ±2.0%
Temperature	-20°C~400°C (-4°F~752°F) ±5.0% (0.1°C/32°F), 400°C~1000°C (752°F~1832°F) ±3.0% (1°C/32°F)
Humidity	30%~95%RH±8.0RH
Light	4000Lux/40000Lux±8.0%
Sound level	45~100db±8db



Sifam Tinsley Instrumentation Inc.
2105 Barrett Park Drive, Unit 105
Kennesaw, GA 30144 (USA)
E-mail Id : psk@sifamtinsley.com
Web : www.sifamtinsley.com
Contact No. : +1 678 881 0008 / 800 879 6171