



Technical Data Sheet

VA8010

*Environmental Meter
Temperature and Humidity*



Application

The meter is a temperature and humidity measuring instrument. It is normally used to measure the humidity and temperature in offices, storerooms, buildings and greenhouses.

Product Features

Display	4 digits LCD Display
Data Hold	√
Dew point temperature	√
Auto Power Off	About 20min
Power	1.5V Battery (AAA)X3
Size	121x60x30 mm (4.76x2.36x1.18 inch)
Weight	~ 180g (6.34 Ounces)

Product Specifications

Measurement Parameters	°C, °F, %RH (relative humidity), td (dew point temperature)
Measuring Range	-10~+50°C, +14~+122°F, 0~100%RH
Accuracy	±1.0°C, ±1.8°F, ±3%RH (5~95%RH)
Resolution	0.1°C, 0.1°F, 0.1%RH
Sample Rate	1 time sec

Accessories Included

Free 1.5V x3 AAA batteries
Free protect cover
Free protective carrying case
Free Wrist / String
User Manual



Sifam Tinsley Instrumentation Inc.
 2105 Barrett Park Drive, Unit 105
 Kennesaw, GA 30144 (USA)
E-mail Id : psk@sifamtinsley.com
Web : www.sifamtinsley.com
Contact No. : +1 678 881 0008 / 800 879 6171