



Technical Data Sheet

VA16

*3 in 1 Digital
multi-tester*



Application

VA16 is a 3 in 1 digital multi-tester, which combines the functions of Digital Multimeter, Telephone Line Tester and Network Cable Tester.

Product Features

Max. Display	1999
Continuity Test	√
Auto Range	-
Data Hold	√
Relative Measurement	-
Back Light	√
Auto Power Off	-
Diode Test	√
Telephone Line Test	RJ12
Network Cable Test	RJ45
Battery Test	1.5 / 6 / 9V
Power	Battery 6F22 (9V) X1
Size	185x85x44 mm (7.28x3.34x1.73 inch)
Weight	~360g (including battery) (12.70 ounces)

Product Specifications

DC Voltage	200m/2/20/200/700V±1.2%
AC Voltage	200m/2/20/200/700V±1.2%
DC Current	200u/2m/20m/200mA±1.8%,10A±3%
AC Current	200u/2m/20m/200mA±1.8%,10A±3%
Resistance	200/2K/20K/200K/2MΩ0.8% 20MΩ±1.0% 200MΩ±5.0%
Capacitance	-
Frequency	-
Temperature	-
Humidity	-
Light	-
Sound level	-



Sifam Tinsley Instrumentation Inc.
2105 Barrett Park Drive, Unit 105
Kennesaw, GA 30144 (USA)
E-mail Id : psk@sifamtinsley.com
Web : www.sifamtinsley.com
Contact No. : +1 678 881 0008 / 800 879 6171