












## Specifications

Key Characteristics	Catalog Page # 	12
	Product Number	170718
	UPC	888434591451
	UOM	Cartridge of 7 Feet
	Trade Name	PermaSleeve®
	Brand Name	Brady®
	Country of Origin 	Mexico
	HTS Code (Harmonized Tariff Schedule) 	8443.99.2550
	ECCN (Export Commodity Control Number) 	EAR99

Dimensions	Dimensions	0.645 in H
	Height	0.645 in
	Roll Length	7 ft
	Sleeve Size	0.375 in Dia x 7 ft L
	Recovered Diameter	0.125 in
	Diameter as Supplied	0.375 in

Material Characteristics	Material Number 	<a href="#">B-342 (View Technical Data Sheet)</a>
	Material 	Heat-shrink Polyolefin
	Material Properties	Flame-retardant, Heat-shrinkable
	Label Properties	Heat Shrink
	Finish	Matte
	Color	Black on White
	Resistance Properties	Chemical-Resistant, Corrosion-Resistant, Humidity-Resistant, Smear-Resistant, UV-Resistant, Weather-Resistant
	Shrink Ratio 	3:1
	Service Temperature Range °F	-67 °F - 275 °F
	Minimum Service Temperature °F	-67 °F
	Maximum Service Temperature °F	275 °F

Product Features	Application 	Wire and Cable Labeling
------------------	---	-------------------------

Printing Specifications	Print Technology	Thermal Transfer
Compatibility	Printer Compatibility	BMP41, BMP51, BMP53, M511
	Wire Diameter Range	0.125 in to 0.32 in
	Wire Gauge Range 	12 AWG - 4 AWG
Compliance	UNSPSC 	39131502
	California Prop 65 	 WARNING: Cancer - <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863