

TECHNICAL DATA

TL1550B Test Leads with Alligator Clips (Red, Black, Green)



Key features

3 Test Leads connected to Low-Leakage Probes (red, black, green), 3 Alligator Clips (red, black, green), Maximum Jaw Opening: 26 mm (1 in.), Replacement Test Lead Set for the Fluke 1550B Meg Ohm Meter Length (Lead Only): 2.6 m (8.6 feet), Cat II 1000 V, Cat III 600V.

Product overview: TL1550B Test Leads with Alligator Clips (Red, Black, Green)

- 3 Test Leads connected to Low-Leakage Probes (red, black, green)
- 3 Alligator Clips (red, black, green)
- Maximum Jaw Opening: 26 mm (1 in.)
- Replacement Test Lead Set for Fluke 1550C FC 5 kV Digital Insulation Tester and 1555 FC 10 kV Insulation Tester
- Length (Lead Only): 2.6 m (8.6 feet)
- Cat II 1000 V, Cat III 600 V, 5kV DC Max (Probes)
- Cat II 1000 V, Cat III 600 V, 10 amps (Alligator Clips)

Ordering information



Fluke-TL 1550B

Test Leads with Alligator Clips (Red, Black, Green)

Fluke. *Keeping your world up and running.®*

Fluke Corporation
PO Box 9090, Everett, WA 98206 U.S.A.

For more information call:
In the U.S.A. (800) 443-5853
In Canada (800) 36-FLUKE
From other countries +1 (425) 446-5500
www.fluke.com

©2023 Fluke Corporation.
Specifications subject to change without notice.
05/2023

**Modification of this document is not permitted
without written permission from Fluke Corporation.**