

# Product data sheet

Specifications



## communication module Ethercat, Altivar, 100Mbps, 2 x RJ45 connectors

VW3A3601

Product availability: Stock - Normally stocked in distribution facility

Price\*: 300.25 USD

### Main

Range Of Product	Altivar
Product Or Component Type	Communication module
Accessory / Separate Part Category	Communication accessories

### Complementary

Product Compatibility	Lexium 32M
Range Compatibility	Altivar Process Modular Altivar Machine ATV340 except Sercos drives Altivar Machine ATV320 Altivar Process ATV900 Altivar 32 Lexium 32
Communication Port Protocol	EtherCAT
Electrical Connection	2 connectors RJ45
Transmission Rate	100 Mbps
Maximum Cable Distance Between Devices	328.08 ft (100 m) 100 Mbps
Addressing	Logical addressing Node addressing Position addressing
Communication Service	PDO and SDO support Drive profile CiA 402 velocity mode IEC 61800-7-201 (CiA 402) CANopen over EtherCAT (CoE)
Display Type	1 LED input status 1 LED RUN 1 LED error 1 LED output status

### Environment

Standards	IEC 61800-7-201 (CiA 402)
-----------	---------------------------

### Ordering and shipping details

Category	US1PC5118263
Discount Schedule	PC51
Gtin	3606480326714
Returnability	Yes
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.48 in (6.300 cm)
Package 1 Width	1.77 in (4.500 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	2.15 oz (61.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	100
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	14.51 lb(US) (6.580 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

 Pvc Free

## Certifications & Standards

**Reach Regulation** [REACH Declaration](#)

**Eu Rohs Directive** Pro-active compliance (Product out of EU RoHS legal scope)

**China Rohs Regulation** [China RoHS declaration](#)

**Environmental Disclosure** [Product Environmental Profile](#)

**Circularity Profile** No need of specific recycling operations

**California Proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)