

# Product data sheet

## Characteristics

# 9422CSF30

Disconnect mechanism, circuit breaker, cable operated, 150/250A, 3 pole, PowerPacT H and J breaker, 36 inch cable



### Main

Range	9422C
Product	Single Cable Operating Mechanism

### Complementary

Circuit Breaker Type	MG-NSF 2 MG-NSF 3 PowerPact H or J 2 PowerPact H or J 3
Included	Ordered separately
Number of Cables	1
Cable Length	36 in

### Environmental

Product Weight	5.73 lb(US) (2.60 kg)
----------------	-----------------------

### Ordering and shipping details

Category	21732-9422
Discount Schedule	CP1
GTIN	785901353263
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.10 in (18.034 cm)
Package 1 Width	12.70 in (32.258 cm)
Package 1 Length	13.30 in (33.782 cm)
Package 1 Weight	5.73 lb(US) (2.599 kg)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
PVC free	Yes

## Contractual warranty

Warranty	18 months
----------	-----------