

Pushbutton Ø 22 mm silver contact

82-6152.1000



<https://eao.com/p/82-6152.1000>

Your product:



82-6152.1000 Pushbutton Ø 22 mm silver contact

FRONT

Front bezel material: Stainless steel

MOUNTING

Mounting cut-out: Ø 22 mm

OPERATING-/INDICATION PART

Lens optics: opaque

Lens illumination: non illuminative

Lens material: Stainless steel

Lens shape: flush

Lens colour: Silver

ELECTRICAL CHARACTERISTICS

Switching voltage and switching current:

	according to IEC 60947-5-1 (Silver contacts)	
	Service categorie AC-15	
	Voltage	Current
	24 VAC	1 A
	35 VAC	1 A (M12 versio
	110 VAC	1 A
	220 VAC	0.5 A
	Switch rating DC service categorie DC-13 (Silver contacts)	
	Voltage	Current
	24 VDC	0.7 A
	35 VDC	0.5 A (M12 vers
	110 VDC	0.2 A
	220 VDC	0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$ 0,75 ... 0,8

Voltage

120 VAC

240 VAC

24 VAC

Current

5 A

3 A

1 A

Thermal current I_{th}:	5 A
Electric strength:	1500 VAC, 50 Hz 1 minute between life terminals and ground
Rated insulation voltage U_i:	250 V
Rated Operational Voltage U_e:	250 VAC
Electrical lifetime:	50 000 cycles of operation
Pollution degree:	2, according to EN IEC 60947-1
Contacts:	1 C

MECHANICAL CHARACTERISTIC

Operating Travel:	ca. 3 mm
Terminal:	Screw terminal
Switching action:	Momentary
Contact material:	Silver
Switching system:	Snap-action switching element
Weight:	0.018 kg
Tightening torque:	0.5 ... 0.6 Nm, Screw terminal 0.1 Nm
Mechanical lifetime:	1 Mio. cycles of operation
Operating force:	4 N ... 7 N

AMBIENT CONDITION

Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Shock resistance:	Max. 500 m / s ² as per IEC 60068-2-27
Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Storage temperature:	- 40 °C ... + 80 °C
Operating temperature:	- 30 °C ... + 70 °C

CERTIFICATE


Conformities: CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

Approbations: CB, CCC, C UL, UL


OTHER

Short Description: Pushbutton Ø 22 mm silver contact, Momentary, 1 C, Screw terminal, Stainless steel, Silver


Component layouts:



Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

