

Illuminated pushbutton Ø 22 mm silver contact

82-6152.1123.B002



<https://eao.com/p/82-6152.1123.B002>

Your product:



82-6152.1123.B002
Illuminated pushbutton Ø
22 mm silver contact

FRONT

Front bezel material: Stainless steel

MOUNTING

Mounting cut-out: Ø 22 mm

OPERATING-/INDICATION PART

Illumination colour: Blue

Lens material: Stainless steel

Shape of illumination: Ring

Lens colour: Silver

Lens optics: opaque

Lens shape: flush

Lens illumination: illuminative

ELECTRICAL CHARACTERISTICS

Electric strength: 1500 VAC, 50 Hz 1 minute between life terminals and ground

Pollution degree: 2, according to EN IEC 60947-1

Operating voltage: 12 V AC/DC

Rated Operational Voltage Ue: 250 VAC

Electrical lifetime: 50 000 cycles of operation

Rated insulation voltage Ui: 250 V

Thermal current Ith: 5 A

Contacts:	1 C		
Switching voltage and switching current:	according to IEC 60947-5-1 (Silver contacts) Service categorie AC-15		
	Voltage		Current
	24 VAC		1 A
	35 VAC		1 A (M12 versio
	110 VAC		1 A
	220 VAC		0.5 A
	Switch rating DC service categorie DC-13 (Silver contacts)		
	Voltage		Current
	24 VDC		0.7 A
	35 VDC		0.5 A (M12 vers
	110 VDC		0.2 A
	220 VDC		0.1 A
	according to UL 508 (Silver contacts)		
	cosφ 0,75 ... 0,8		
	Voltage		Current
	120 VAC		5 A
	240 VAC		3 A
	24 VAC		1 A

MECHANICAL CHARACTERISTIC

Mechanical lifetime:	1 Mio. cycles of operation
Contact material:	Silver
Operating Travel:	ca. 3 mm
Weight:	0.018 kg
Tightening torque:	0.5 ... 0.6 Nm, Screw terminal 0.1 Nm
Operating force:	4 N ... 7 N
Terminal:	Screw terminal
Switching system:	Snap-action switching element
Switching action:	Momentary

AMBIENT CONDITION

Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Operating temperature:	- 30 °C ... + 70 °C
Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Storage temperature:	- 40 °C ... + 80 °C
Shock resistance:	Max. 500 m / s ² as per IEC 60068-2-27

CERTIFICATE

Conformities: CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)

Approbations: CB, CCC, C UL, UL


OTHER

Symbol: Standby


Kind of illumination: Single-LED

Short Description: Illuminated pushbutton Ø 22 mm silver contact, Momentary, 12 V AC/DC, 1 C, Screw terminal, Stainless steel, Blue, Standby, Silver


Mounting cut-outs:



Wiring diagrams:



Component layouts:



Dimension drawings:

