

Actuator

84-1101.0



<https://eao.com/p/84-1101.0>

Your product:



84-1101.0 Actuator

FRONT

Front dimension:	Ø 25 mm
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Mounting cut-out:	Ø 22.5 mm
--------------------------	-----------

OPERATING-/INDICATION PART

Lens illumination:	illuminative
---------------------------	--------------

MECHANICAL CHARACTERISTIC

Operating Travel:	1.2 mm
Weight:	0.003 kg
Switching action:	Momentary
Switching system:	Short-travel element
Mechanical lifetime:	≥1 Mio. cycles of operation
Operating force:	4.0 N ±0.2 N
Tightening torque:	Fixing nut 0.8 Nm

AMBIENT CONDITION

IP front protection:	IP67
IP Protection:	IP67

Operating temperature: - 25 °C ... + 70 °C

Storage temperature: - 40 °C ... + 85 °C

Climate resistance: Damp heat, cyclic: 96 hours, + 25 °C/97 %, + 55 °C/93 % relative humidity, as per EN IEC 60068-2-30
Damp heat, steady: 56 days, + 40 °C/93 % relative humidity, according to EN IEC 60068-2-78
Rapid change of temperature: 100 cycles, - 40 °C ... + 80 °C, as per EN / IEC 60068-2-14

CERTIFICATE

Approbations: EBC (TSI PRM), NFF

Conformities: CE, UKCA, 2011 / 65 / EC (RoHS)

OTHER


Short Description: Actuator, Ø 22.5 mm, Ø 25 mm, illuminative, Black, Plastic, Momentary, IP67

Dimension: Ø 25 mm


Housing colour: Black

Housing material: Plastic

Mounting cut-outs:



Wiring diagrams:



Dimension drawings:

