


# Plastic tubing PUN-H-4X0,75-TSW

Part number: 8048673

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value   |
|--|---|
| Outside diameter                                   | 4 mm  |
| Bending radius relevant for flow rate              | 16 mm   |
| Inside diameter                                    | 2.6 mm  |
| Min. bending radius                                | 8 mm  |
| Application note                                   | TPE-U Ether based   |
| Tubing characteristics                             | Suitable for energy chains  |
| Operating pressure for entire temperature range    | -0.095 MPa ... 0.6 MPa  |
| Operating pressure for entire temperature range    | -0.95 bar ... 6 bar   |
| Operating pressure for entire temperature range    | -13.775 psi ... 87 psi  |
| Temperature-dependent operating pressure           | -0.095 MPa ... 1 MPa  |
| Temperature-dependent operating pressure           | -0.95 bar ... 10 bar  |
| Temperature-dependent operating pressure           | -13.775 psi ... 145 psi   |
| Information on operating pressure                  | Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60 °C   |
| Certification                                      | German Technical Control Board (TÜV)  |
| Certificate issuing authority                      | B 013277 0506 00  |
| Operating medium                                   | Compressed air as per ISO 8573-1:2010 [7:-:-]<br>Water (liquid, ice-free)   |
| Material fire test                                 | UL94 HB   |
| LABS (PWIS) conformity                             | VDMA24364-B2-L  |
| Suitability for the production of Li-ion batteries | Metals with more than 1% by mass of copper, zinc or nickel by mass are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils |
| Cleanroom class                                    | Statically installed element, no meaningful evaluation possible according to ISO 14644-1  |
| For use in the food industry                       | See supplementary material information  |
| Ambient temperature                                | -35 °C ... 60 °C  |
| Product weight by length                           | 0.0085 kg/m   |
| Pneumatic connection                               | For plug connection outside diameter 4 mm<br>For barbed fitting, inside diameter 3 mm, with union nut   |
| Color  | Translucent black   |
| Shore hardness                                     | D 52 +/-3   |
| Note on materials                                  | RoHS-compliant  |
| Material of pneumatic tubing                       | TPE-U(PU)   |