


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/28/05	M.LAHEY
B	ECN 5336: RE-MODELED AND RE-DIMENSIONED, NEW FORMAT	2/22/11	D.FRISIELLO



NOTE:
 BNC PLUGS MUST BE INSTALLED ON BOTH JACKS OF AN ADAPTER TO DISCONNECT 50-OHM TERMINATING RESISTOR BETWEEN OUTER SHELL AND CENTER CONDUCTOR. RESISTOR HAS 1/8 WATT RATING AND IS INTENDED TO TERMINATE CABLES FOR SIGNAL LEVEL ENERGY ONLY.

- NOTES:
1. MATERIAL: .06 THICK COLD ROLLED STEEL.
 2. PANEL FINISH: FLAT BLACK POWDER COAT.
 3. SILKSCREEN COLOR: WHITE.
 4. PANEL SHALL BE PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0014.
 5. (16) BNC AUTO-TERMINATING FEED-THROUGH ADAPTERS HAVE GOLD PLATED CONTACTS AND HAVE INSULATED BUSHINGS TO ISOLATE THEM FROM THE PANEL.

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +3% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 .XX = ± .02 .XXX = ± .005	APPROVALS DRAWN BY M.LAHEY CHECKED BY D.PARHAM APPROVED BY C.MCCORMICK	DATE 11/28/05 11/28/05 11/28/05	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
PROJECTION 	COLOR VARIATIONS MAY OCCUR	SIZE A	PRODUCT DESCRIPTION 1.75"X19" W/16 BNC AT BLK
SCALE: NONE		FSCM NO. 43321	DWG. NO. PR175BX16GBLK
CAD FILE: PR175BX16GBLK.SLDDRW		SHEET 1 OF 1	