



SIEMENS LOW VOLTAGE PL SERIES LOAD CENTER. FACTORY INSTALLED MAIN BREAKER WITH 42 1-INCH SPACES ALLOWING MAX 60 CIRCUITS. 3-PHASE 4-WIRE SYSTEM RATED 120/240V OR 120/208V (200A) 22KA INTERRUPT. SPECIAL FEATURES: COPPER BUS, INTERCHANGEABLE MAIN, GRAY TRIM, NEMA TYPE1 ENCLOSURE FOR INDOOR USE.

General technical data	
configuration of the busbars	200A
fastening method	Combination
phase number	3
suitability for operation	Residential
Electricity	
ampacity	200 A
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	240 V
Breaking Capacity	
switching capacity current according to EN 60898 rated value	22000 A
Model	
product brand name	Siemens
product sub brand name	Loadcenter
product type designation	1
type of wiring of distribution board	3/4W
Mechanical Design	
number of modular width units for installation width	42
size of the circuit-breaker	MB

last modified:

12/8/2023 

