



Siemens Low Voltage Residential Circuit Breakers Miniature Circuit Breakers GFCI - Equipment Protect 2-pole plug-on 10k are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Sub Brand: N/A Type: QE Special Features: N/A Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120/240 V Amperage Rating: 15A Load Rating: N/A Frequency Rating: N/A Phase: N/A Frame: N/A Trip Type: N/A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 2P *Being obsoleted - order US2:Q215EG*

General technical data	
number of poles	2
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	15 A
Model	
product brand name	SIEMENS
type of electrical connection	PLUG-IN
Mechanical Design	
depth [in]	3 in
design of the product	QE
height [in]	6 in
width [in]	4 in
General product approval	
standard	UL 489

last modified:

1/6/2021

