

# 320 Series True-rms Clamp Meters

Fluke rugged. Fluke precise. Fluke reliable.

The Fluke 323, 324 and 325 Clamp Meters are designed to perform in the toughest environments and provide noise-free, reliable results users can trust to confidently diagnose problems. True-rms measurements and optimized ergonomics make the 320 Series Clamp Meters the best general troubleshooting tools for commercial and residential electricians.

**New**



## Technical Data

### Measurement capability

- 400 A ac current measurement (ac and dc current; 325 only)
- 600 V ac and dc voltage measurement
- True-rms ac voltage and current for accurate measurements on non-linear signals
- Resistance measurement to up to 40 k $\Omega$  with continuity detection
- Temperature and capacitance measurement (324 and 325 only)
- Frequency measurement (325 only)

### Features

- Slim, ergonomic design
- Large, easy to read backlight display (324 and 325 only)
- CAT IV 300 V/CAT III 600 V safety rating
- Hold button
- Two-year warranty
- Soft carrying case

## Specifications

		<b>323</b>	<b>324</b>	<b>325</b>
<b>AC current</b>	Range	400.0 A	40.00 A/400.0 A	40.00 A/400.0 A
	Accuracy	2 % ± 5 digits (45 Hz to 65 Hz) 2.5 % ± 5 digits (65 Hz to 400 Hz)	1.5 % ± 5 digits (45 Hz to 400 Hz) Note: Add 2 % for position sensitivity	2 % ± 5 digits (45 Hz to 65 Hz) 2.5 % ± 5 digits (65 Hz to 400 Hz)
<b>DC current</b>	Range	—	—	40.00 A/400.0 A
	Accuracy	—	—	2 % ± 5 digits
<b>AC voltage</b>	Range	600.0 V	600.0 V	600.0 V
	Accuracy	1.5 % ± 5 digits	1.5 % ± 5 digits	1.5 % ± 5 digits
<b>DC voltage</b>	Range	600.0 V	600.0 V	600.0 V
	Accuracy	1.0 % ± 5 digits	1.0 % ± 5 digits	1.0 % ± 5 digits
<b>Resistance</b>	Range	400.0 Ω/4000 Ω	400.0 Ω/4000 Ω	400.0 Ω/4000 Ω/40.00 kΩ
	Accuracy	1 % ± 5 digits	1 % ± 5 digits	1 % ± 5 digits
<b>Continuity</b>		≤ 70 Ω	≤ 30 Ω	≤ 30 Ω
<b>Capacitance</b>		—	100.0 μF to 1000 μF	100.0 μF to 1000 μF
<b>Frequency</b>		—	—	5.0 Hz to 500.0 Hz
<b>AC response</b>		True-rms	True-rms	True-rms
<b>Backlight</b>		—	Yes	Yes
<b>Data hold</b>		Yes	Yes	Yes
<b>Contact temperature</b>		—	-10.0 °C to 400.0 °C (14.0 °F to 752.0 °F)	-10.0 °C to 400.0 °C (14.0 °F to 752.0 °F)
<b>Min/Max</b>		—	—	Yes
<b>Size</b>	H x W x D (mm)	207 x 75 x 34	207 x 75 x 34	207 x 75 x 34
	Max wire diameter	30 mm (600 MCM)	30 mm (600 MCM)	30 mm (600 MCM)
	Weight	265 g	208 g	283 g
<b>Category rating</b>		CAT III 600 V CAT IV 300 V	CAT III 600 V CAT IV 300 V	CAT III 600 V CAT IV 300 V
<b>Warranty</b>		Two-year	Two-year	Two-year

### Ordering information

**323** True-rms Clamp Meter

**324** True-rms Clamp Meter

**325** True-rms Clamp Meter

### Included with all models

Clamp meter, test leads, soft case, and users manual.

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**Fluke Europe B.V.**  
PO Box 1186, 5602 BD  
Eindhoven, The Netherlands

**For more information call:**  
In the U.S.A. (800) 443-5853 or  
Fax (425) 446-5116  
In Europe/M-East/Africa +31 (0) 40 2675 200 or  
Fax +31 (0) 40 2675 222  
In Canada (800)-36-FLUKE or  
Fax (905) 890-6866  
From other countries +1 (425) 446-5500 or  
Fax +1 (425) 446-5116  
Web access: <http://www.fluke.com>

©2012 Fluke Corporation.  
Specifications subject to change without notice.  
Printed in U.S.A. 5/2012 4217271A\_EN

**Modification of this document is not permitted without written permission from Fluke Corporation.**