


FEATURES

- UL approved Nylon 66, 94V-2
- Color: Natural, other special colors are available upon request.
- The cable tie can be secured to panel with a single bolt.

RS PRO Mounting Cable Tie

RS Stock No.: 2243198



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

- Material: UL approved Nylon 66 , 94V-2.
- Color: Natural
- The cable tie can be secured to panel with a single bolt.

General Specifications

Series	Mounting Cable Tie
Type	Non-Releasable
Colour	Natural
Material	Nylon 66
Finish	
Application	
Resistant To	
UV Resistant	No
Minimum Operating Temperature	-40°C
Maximum Operating Temperature	85°C
Fire Behaviour	Self-Extinguishing
Quantity	100

Mechanical Specifications

Length	219mm(8 11/16")
Width	4.8mm
Max. Bundle Dia.	52mm
Hole Dia	5.0mm
Tensile Strength	75lbs/34kgs
Thickness	1.3±0.25mm

Protection Category

IP Rating

Classification

eCl@ss (10.0.1)

UNSPSC (6.01)

Approvals

Declarations

Standards Met

UL, RoHS, SVHC, HF, ABS, DNV

Similar Products

Stock No.	Brand	Product Name	Colour	Material	Tensile strength
601-091	RS	Mounting Cable Tie	Natural	Nylon66	50lbs/22kgs
601-108	RS	Mounting Cable Tie	Natural	Nylon66	120lbs/55kgs

