

Datasheet

RS Pro Plain Stainless Steel Internal Tooth Locking and Anti-Vibration Washer, M20, 304, A2

RS Stock No: **187-0664**



Product Details

RS Pro internal tooth shake-proof washer has A2, 304 plain stainless steel construction for durability. This internal tooth shake-proof, locking and anti-vibration washer is suitable for screw or bolt size of M20.

Features and Benefits

- A2, 304 plain stainless steel construction
- Shake-proof washer - internal
- Locking and anti-vibration washer



ENGLISH

Specifications:

| | |
|----------------------|-----------------|
| Finish | Plain |
| Material | Stainless Steel |
| Washer Type | Internal Tooth |
| For Screw/Bolt Size | M20 (Form J) |
| Inside Diameter | 21 mm |
| Outside Diameter | 33 mm |
| Stainless Steel Type | 304 (A2) |
| Thickness | 1.4 mm |
| Specification | DIN 6797 |