

Datasheet

19-inch Front Panel, 3U, 8hp, Grey, Aluminium



RS Stock number 543-172

STANDARD TYPE 3U AND 6U

- Two versions, available in comprehensive range of widths
- Supplied in kit or bulk pack form
- Conforms to IEC 60297-3 and DIN 41494

Version 1 has anodised front and inner faces. The method of manufacture produces cut edges which are invisible in normal use. Material grain is horizontal. The kit includes as standard plastic retaining inserts, which can be replaced with a metal type.

Version 2 has an anodised front face and a chromated, conductive inner face for grounding purposes. Supplied with metal retaining inserts as standard.

BULK PACKING

Subject to minimum quantities, we can supply front panel kits in bulk, offering savings in packaging and unpacking time. Please specify 'BULK PACK' when ordering.

CONTENTS OF KITS

Item	Description	Material
1	Front panel	2,5mmg ALMg3 1/2 hd
2	Handle	Luranylo 2452/1, black
3	Ident label	1,5mmg A1Mg3 1/2 hd anodised
4	Screw M2, 5 x 16	
5	Screw M2, 5 x 7	
6	Special screw M2,5 x 11	
7	Nut M2,5	
8	Shakeproof washer M2,5	
9	Retaining insert	See Text
Assembly instructions		

ORDERING INFORMATION

Description: Standard front panels - 3U

Panel width	Dim 'A'	Dim 'B'	Order code	
			Version 1	Version 2
3HP	14,8	-	957-235347	953-235335
4HP	19,9	-	957-235348	953-235336
5HP	25,0	-	957-235349	953-235339
6HP	30,1	-	957-235351	953-235340
7HP	35,2	-	957-235352	953-235341
8HP	40,2	-	957-235353	953-235342
9HP	45,3	-	957-235354	953-235376
10HP	50,4	35,6	957-235355	953-235343
12HP	60,6	45,7	957-235356	953-235344
14HP	70,7	55,9	957-235357	953-235345
21HP	106,3	91,4	957-235358	953-235346
24HP	121,5	106,7	957-235359	-
42HP	213,0	198,1	957-235360	-
84HP	426,3	411,5	957-236065*	-

Description: Standard front panels - 6U

4HP	19,9	-	957-235460	953-235442
5HP	25,0	-	957-235460	-
6HP	30,1	-	957-235461	953-235444
7HP	35,2	-	957-235462	-
8HP	40,2	-	957-235463	953-235446
10HP	50,4	35,6	957-235465	-
12HP	60,6	45,7	957-235466	953-235440
14HP	70,7	55,9	957-235467	-
24HP	121,5	106,7	957-235469	-
42HP	213,0	198,1	957-235470	-
84HP	426,3	411,5	957-236073*	-

* This item has no handles



Standard 3U & 6U front panels

