

FEATURES

- 1 Gang
- Unswitched
- Twin Earth
- 13A Fused
- With Flex Outlet
- 20mm Knockouts
- Surface Mounting

RS PRO Fused Spurs

RS Stock No.: 2554749



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Fused Spurs

Product Description

13A 1 Gang DP Fused Spur

- Supplied with 40mm deep mounting box
- Suitable for domestic and light commercial installations
- Electrophoretically coated plate and back box
- Suitable for conduit installations
- Optional flex outlet is available through the front of the plate
- Flex outlet has cable restraint fitted

General Specifications

Dimensions (mm)	80 (W) x 80 (H) x 42 (D)
Plate Fixing Centres (mm)	60.3
Style	Metal Clad
Finish	Metal Clad Grey
Insert Colour	White (WH)
Warranty (Years)	10

Mechanical Specifications

Fuse Fitted Rating & Type	13A (BS 1362)
Termination Type	Screw
Terminal Size (mm)	Ø5
Terminal Torque Value (Nm)	2
Terminal Capacity - Solid (mm²)	3 x 2.5 or 2 x 4
Twin Earth Terminals	Yes
Flex Outlet Available	Yes
Flex Outlet Location	Front of Plate
Switched	No
Supplied Back Box Depth (mm)	40
Back Box Knockouts - Total (mm)	5 x Ø20
Back Box Earth Terminal Supplied	Yes
Operational Temperature (°C)	-5 to +40

Electrical Specifications

Rated Voltage (V~) (Ue)	250
Frequency (Hz)	50
Resistive Load Rating (A)	13

Approvals

Standards Met	BS 1363-4, BS 1362
----------------------	--------------------