

Main

Product	Surge protection device
Range	Surgelogic

Complementary

Voltage Rating	480 V delta AC
MCOV	180 V
SCCR	200 kA
Surge Current	40 kA
Nominal Discharge Current	10 kA
Number of Phases	3 phase
Wiring Configuration	3-wire
Connection	Wire AWG 12 copper
Local Signalling	Status LED normal operation
Cable length	24 in (609.6 mm)
Mounting Support	Panel mounting
Height	3.07 in (78 mm)
Width	3.6 in (92 mm)
Depth	2.6 in (67 mm)

Environment

Ambient Operating	149 °F (65 °C)
Enclosure Rating	NEMA 4X
Enclosure Material	Black Plastic
Standards	UL 1449:ed. 4 CSA C22.2 No 8:1986

Ordering and shipping details

Category	US1DE1B08462
Discount Schedule	DE1B
GTIN	785901599920
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.100 in (12.954 cm)
Package 1 Width	4.0000000000 in (10.16 cm)
Package 1 Length	3.400 in (8.636 cm)
Package 1 Weight	15.040 oz (426.377 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes