



Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	PoN Convertible Mains (breaker)
Rated Current	200 A
Number of Spaces	8
Maximum Number of Single Pole Circuits	16
Enclosure Rating	NEMA 3R weatherproof enclosure
Cover Type	Surface cover
Electrical Connection	Feed-thru lugs
Provided Equipment	Circuit-breaker 1) 2P 200 A 120/240 V AC main supply ready assembled

Complementary

Max Short Circuit Current Rating	22 kA
Maximum Number of Tandem Breakers	8
Number of Phases	1 phase 3 wires
Voltage Rating	120/240 V AC
Wire Size	AWG 4...250 kcmil copper or aluminium
Ground Bar	Grounding bar (ordered separately)
Busbar Material	Tin plated aluminium: busbar
Enclosure Material	Welded galvanized steel
Surface Finish	Baked enamel Gray
Box Number	6R
Bus Rated Current	225.0 A
Height	29.8 in (758 mm)
Width	14.8 in (375 mm)
Depth	4.5 in (115 mm)

Environment

Ambient Air Temperature for Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL listed file E-6294

Ordering and shipping details

Category	US1DE3C00149
Discount Schedule	DE3C
GTIN	785901973959
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.800 in (12.192 cm)
Package 1 Width	15.400 in (39.116 cm)
Package 1 Length	31.900 in (81.026 cm)
Package 1 Weight	33.519 lb(US) (15.204 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Height	43.500 in (110.490 cm)
Package 2 Width	40.0000000000 in (101.600 cm)
Package 2 Length	48.0000000000 in (121.920 cm)
Package 2 Weight	784.800 lb(US) (355.979 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations