

## Main

Product	Electrically Held Lighting Contactor
Type	S

## Complementary

Control Circuit Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Current Rating	30 A
Number of Poles	2P
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Options	None
Electrical Connection	Lugs
Height	3.5 in (89 mm)
Depth	4.2 in (107 mm)
Width	3.2 in (82 mm)

## Environment

Enclosure Type	Not rated (open device) surface none
Product Certifications	UL Listed[RETURN]CSA

## Ordering and shipping details

Category	US10CP121325
Discount Schedule	0CP1
GTIN	785901619536
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 in (11.4 cm)
Package 1 Width	5.9 in (15.0 cm)
Package 1 Length	8.0 in (20.3 cm)
Package 1 Weight	3.02 lb(US) (1.37 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not compliant
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------