



## Main

Product or Component Type	Electrically Held Lighting Contactor
Range of Product	8903L
Control Circuit	Separate control circuit

## Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	25 VA 60 Hz 150 VA 50 Hz
Hold-in power consumption in VA	30 VA 60 Hz 30 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	2P 2 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	12.7 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.8 in (198 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed[RETURN]CSA

## Ordering and shipping details

Category	US10CP121321
Discount Schedule	0CP1
GTIN	785901851226
Returnability	Yes
Country of origin	MX

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.09 in (18.0 cm)
Package 1 Width	8.3 in (21.1 cm)
Package 1 Length	13.7 in (34.8 cm)
Package 1 Weight	9.55 lb(US) (4.33 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	50
Package 2 Height	40.0000000000 in (101.6 cm)
Package 2 Width	40.0000000000 in (101.6 cm)
Package 2 Length	48.0000000000 in (121.92 cm)
Package 2 Weight	482.434 lb(US) (218.828 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------