

Product data sheet

Characteristics

2510KO1

Switch, manual, 30A, 2 pole, 3 HP at 575 VAC, single phase, toggle operated, no indicator, open style

Main

Product	Single Unit Manual Switch
Type	K

Complementary

Current Rating	30 A
Horsepower Rating	2 Hp 115 V AC 2 Hp 230 V AC 3 Hp 460 V AC 3 Hp 575 V AC 1 Hp 90 V DC 2 Hp 115 V DC 1.5 hp 230 V DC
Maximum Voltage Rating	600 V AC 230 V DC
Number of Poles	2P
Control Unit Type	Toggle
Number of Phases	1 phase
Pilot Light	No indicator
Starter Type	Non reversing
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 14...AWG 10 copper
Height	4.13 in (104.90 mm)
Width	1.69 in (42.93 mm)
Depth	2.34 in (59.44 mm)
Net Weight	0.35 lb(US) (0.16 kg)

Environment

Certifications	UL recognized E42243 CCN NLRV2[RETURN]CSA LR25490 class 3211 05
NEMA Enclosure Rating	Not rated (open device)

Ordering and shipping details

Category	US10CP121102
Discount Schedule	OCP1
GTIN	785901554554
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.900 in (4.826 cm)
Package 1 Width	3.0000000000 in (7.620 cm)
Package 1 Length	4.700 in (11.938 cm)
Package 1 Weight	5.600 oz (158.757 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	72
Package 2 Height	12.600 in (32.004 cm)
Package 2 Width	12.600 in (32.004 cm)
Package 2 Length	15.0000000000 in (38.100 cm)
Package 2 Weight	31.680 lb(US) (14.370 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	1152
Package 3 Height	40.0000000000 in (101.600 cm)
Package 3 Width	40.0000000000 in (101.600 cm)
Package 3 Length	48.0000000000 in (121.920 cm)
Package 3 Weight	507.000 lb(US) (229.971 kg)

Offer Sustainability

California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------