

VH322DSGL

Safety switch, VisiPacT, heavy duty, fused, viewing window, NEMA 4X, 240V, 60A, 3 pole, ground lugs



Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Field installed kit available
Number of Poles	3
Current Rating	60 A
Voltage Rating	250 V DC 240 V AC
Enclosure Rating	NEMA 4X stainless steel 304
Motor power hp	3 Hp at 240 V AC 50-60 Hz for 1 phase motors 7.5 Hp at 240 V AC 50-60 Hz for 3 phase motors 10 Hp at 240 V AC 50-60 Hz for 1 phase motors 15 Hp at 240 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC

Complementary

Short-circuit current	10 KA for H, K, J or R without fuse rejection clips 200 KA for R with fuse rejection clips 200 kA for J
Fuse type	H or K R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring configuration	3-wire
Wire Size	AWG 14...AWG 3 copper AWG 12...AWG 3 aluminium
Tightening torque	50 Lbf.in (5.6 N.m) (AWG 3) 45 Lbf.in (5.08 N.m) (AWG 6...AWG 4) 40 Lbf.in (4.5 N.m) 0.013 in ² (8.367 mm ²) (AWG 8) 50 lbf.in (5.6 N.m) 0.003...0.008 in ² (2.06...5.261 mm ²) (AWG 14...AWG 10)
Depth	5.384 in (136.754 mm)
Width	7.22 in (183.39 mm)
Height	14.93 in (379.22 mm)
Net Weight	13.2 lb(US) (6 kg)
Grounding Kit	Factory installation
Service Entrance	Suitable service entrance for USA Suitable service entrance for Mexico

Environment

Certifications	cULus Listed File E2875
Standards	UL98 CSA C22.2 No 4 NOM-003-SCFI-2000

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	US10DE100010
Discount Schedule	0DE1
GTIN	3606485893556
Returnability	Yes
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.50 in (13.97 cm)
Package 1 Width	8.875 in (22.542 cm)
Package 1 Length	16.625 in (42.227 cm)
Package 1 Weight	13.2 lb(US) (6 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	"WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov "
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations