



SIEMENS LOW VOLTAGE METER MAIN. FACTORY INSTALLED MAIN BREAKER 2 (1 INCH) SPACES INTERIOR ALLOWING MAX 2 CIRCUITS. 5-JAW METER / 1-PHASE SYSTEM RATED 200A. SPECIAL FEATURES: OH/UG FEED, RINGLESS TYPE COVER, HORN BYPASS SOCKET

General technical data	
cable entry type	OH/UG
fastening method	Surface
Electricity	
ampacity	200 A
Model	
product brand name	Siemens
special product feature	Horn Bypass
Mechanical Design	
design of the terminal strip	Tin-plated aluminum extrusions 6061-T6
General product approval	
certificate of suitability	UL67

last modified:

5/9/2023 

