



Siemens Low Voltage Residential Circuit Breakers Miniature Thermal Mag Circuit Breakers - Surge are Circuit Protection Load Center Mains, Feeders, and Miniature Circuit Breakers. Type: SPD Standard: UL Listed, CSA Certified Voltage Rating: 120/240 Amperage Rating: 15 Interrupt Rating: 10 Operating Temperature: 40

Electricity	
continuous current rated value	20 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	40 °C
Model	
product brand name	SIEMENS
Mechanical Design	
design of the product	SPD
General product approval	
standard	UL Listed, CSA Certified

last modified:

1/6/2021 

