



Siemens Low Voltage Talon Meter Sockets Residential - Talon Meter Sockets UAT1 Steel are Residential Enclosures Single-Family Metering. Type: UAT1 Special Features: NO BYPASS Application: RESIDENTIAL Standard: UL Voltage Rating: 300V Amperage Rating: 135A Phase: 1 OR 3 PHASE Size: 5.000X8.800X13.400 Cable Entry: OH Terminal: 5 TERMINALS Mounting: SURFACE MOUNTING Operating Temperature: AVERAGE AMBIENT Enclosure: STEEL

General technical data	
cable entry type	OH
fastening method	SURFACE MOUNTING
suitability for operation	RESIDENTIAL
Electricity	
ampacity	135 A
voltage between phase and phase rated value	300 V
Model	
product brand name	MURRAY
product type designation	UAT1
special product feature	NO BYPASS
Mechanical Design	
depth [in]	13.4 in
design of the terminal strip	5
height [in]	5 in
width [in]	8.8 in
General product approval	
certificate of suitability	UL

last modified:

6/26/2022 

