

Siemens Low Voltage Power Panels - Unassembled P4 Power Panel are Power Distribution Power Panels. Sub Brand: Panelboards Type: Accessory Application: Unassembled Panelboard Standard: UL67 Voltage Rating: 480/277V Amperage Rating: 1200A Phase: 3P Frequency Rating: 60H Short Circuit Rating: 100kA Connection: ABC Material: CU/AL Mounting: Bolted Operating Temperature: Average Ambient Consist Of: MLO Lug Kit :

General technical data	
maximum short-circuit current breaking capacity (Icu) at AC rated value	100 A
suitability for operation	Unassembled Panelboard
Electricity	
supply voltage frequency rated value 50/60 Hz	Yes
Model	
product brand name	Siemens
product sub brand name	Panelboards
product type designation	Accessory
type of electrical connection	ABC
Mechanical Design	
material of the enclosure	CU/AL
General product approval	
certificate of suitability	UL67

last modified:

6/26/2022 

