



Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL98/CSA/NFPA 79 V. Rating: 600V A. Rating: 100A No. Of poles: 3P F. Rating: 60 Hz Action: single throw Mounting: PANEL MOUNTING. O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

| General technical data | |
|---|-----------------------|
| fastening method | PANEL MOUNTING |
| Electricity | |
| voltage between phase and phase rated value | 600 V |
| Model | |
| product brand name | SIEMENS |
| product type designation | OEM DISCONNECT SWITCH |
| General product approval | |
| certificate of suitability | UL98/CSA/NFPA 79 |

last modified:

1/6/2021

