



Breaker BQD 3P 15A 480V AC 14kA

| General technical data | |
|---|------------------------------|
| number of poles | 3 |
| suitability for operation | CONSTRUCTION |
| Electricity | |
| continuous current rated value | 15 A |
| supply voltage frequency rated value 50/60 Hz | Yes |
| Environmental conditions | |
| ambient temperature during operation maximum | 40 °C |
| Model | |
| product brand name | Siemens |
| special product feature | PANELBOARD MOUNT |
| type of electrical connection | LOW TAB |
| Mechanical Design | |
| depth [in] | 4 in |
| design of the overload release | THERMAL MAGNETIC TRIP UNIT |
| design of the product | BQD |
| height [in] | 3 in |
| material of the enclosure | MOLDED CASE CIRCUIT BREAKER |
| size of the circuit-breaker | 100A |
| width [in] | 3 in |
| General product approval | |
| standard | UL 489 CSA-C22.2 IEC 60947-2 |

last modified:

12/20/2023

