

FirstSurge type 2 surge protective device. Rated 120/240V split phase (Up to 400A) at 50/60Hz. Surge spike capacity 100kA. Special features: less than 1 nanosecond response time, Nema 4X enclosure (indoor - outdoor), 3 stage commercial grade notification, ground reference monitoring (GRM), installs onto any brand load center



General technical data	
fastening method	Surface
phase number	1
suitability for operation	Residential
Electricity	
supply voltage frequency rated value 50/60 Hz	Yes
voltage between phase and Ground (GND) rated value	120 V
voltage between phase and phase rated value	241 V
Model	
product brand name	Siemens
product sub brand name	FirstSurge
type of electrical connection	Wired
Mechanical Design	
depth [in]	3 in
height [in]	8 in
material	CONTACT MANUFACTURER
width [in]	4 in
General product approval	
certificate of suitability	UL 1449

last modified:

5/19/2022 

