



## NOVAX®

### Class 3 Rubber Insulating Glove with Contour Cuff - 18"

- Contoured shape reduces hand fatigue
- Natural rubber construction offers the required dielectric properties combined with flexibility, strength and durability
- Contour cuff for increased mobility and comfort on the job
- Silicone free
- Individually numbered for traceability and stamped with factory manufacturing date

## Applications

- Power Generation
- Electrical Contractors
- Plant Maintenance
- Utility Work
- Hybrid Automotive Repair, Service and Manufacturing

## Technical Data

Color	Black
Sizes Available	9-12
Packaging	Boxed
Packed	6 Pair/Case
Case Dimensions (in)	21.14 x 18.15 x 11.89
Case Weight (lbs)	14.70
Country of Origin	Malaysia
Material	Rubber
Length	18"
Cuff	Contour
Cuff Color	Yellow
Construction	--
Certifications	NFPA 70E, ASTM D120, Silicone Free
Product Circularity	--

## Performance Data

Electrical Class	Class 3
------------------	---------

## Care Instructions

Wash in warm water (29°C/85°F) with mild detergent and disinfect with a small amount of chlorine bleach. Air or tumble dry at low heat (74°C/165°F). Gloves may be dusted lightly with talc to reduce tackiness. Gloves should be stored in a glove bag, finger tips up, hung and not laid flat. Leather protecting glove should be removed before storage. Never fold gloves. Store in as dry and cool (35°C/95°F maximum) location as possible, away from sources of ozone and direct sunlight.



## SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
151-3-18/9	Black	9	616314116940	01616314116949	02616314116948
151-3-18/9.5	Black	9.5	616314146749	01616314146748	02616314146747
151-3-18/10	Black	10	616314116919	01616314116918	02616314116917
151-3-18/10.5	Black	10.5	616314146725	01616314146724	02616314146723
151-3-18/11	Black	11	616314116926	01616314116925	02616314116924
151-3-18/11.5	Black	11.5	616314146732	01616314146731	02616314146730
151-3-18/12	Black	12	616314116933	01616314116932	02616314116931