BT1.5I-M





- For indoor use
 - Dome-top head features unique patented design with round, smooth edges
 - Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range
 - High strength and low thread force
 - Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Light-Heavy cross section ties have a straight tip)

| ■ Part Number | BT1.5I-M |
|--|---|
| ■ RoHS Compliancy Status | |
| | Compliant |
| ■ Part Description | Cable Tie with metal barb, 6.1", Intermediate cross section |
| ■ Product Type | Cable Ties |
| Material | Nylon 6.6 |
| ■ Color | Natural |
| CSA Certified | Yes |
| ■ Mil. Std. Part Number | MS3367-5-9 |
| ■ UL Listed (File #E56854) | Yes |
| ■ UL Recognized (File #E56854) | Yes |
| ■ Length (In.) | 6.1 |
| ■ Length (mm) | 155 |
| ■ Width (In.) | .141 |
| ■ Width (mm) | 3.6 |
| - CE Compliant | Yes |
| Cross Section | Intermediate |
| ■ Head Height (In.) | .185 |
| ■ Head Height (mm) | 4.7 |
| ■ Head Width (In.) | .248 |
| ■ Head Width (mm) | 6.3 |
| ■ Locking Style | Locking |
| Material Flammability Rating | UL 94V-2 |
| ■ Max. Bundle Diameter (In.) | 1.50 |
| Max. Bundle Diameter (mm) | 38 |
| ■ Max. Continuous Use Temperature | e 185°F (85°C) |
| ■ Min. Loop Tensile Strength (Lbs.) | 40 |

| 178 |
|--|
| Cable Tie, Metal Barb, 6.1"L (155mm), Intermediate, Nylon, Natural |
| .041 |
| 1.0 |
| GTS, GTSL, GS2B, PTS, PPTS, STS2 |
| PC |
| 1000 |
| |

■ BOM Qty. (# of Pkgs.)

