3RU1116-1GC1 Page 1

SIEMENS

Product data sheet 3RU1116-1GC1




OVERLOAD RELAY, 4.5...6.3 A, 1NO+1NC, SIZE S00, CLASS 10, CAGE CLAMP CONNECTION, FOR INSTALLAT. AS A SINGLE UNIT

General technical details:		
Operating current / of the fuse link / rated value	20 A	
Adjustable response current / of the current-dependent overload release / initial value	4.5 A	
Adjustable response current / of the current-dependent overload release / final value	6.3 A	
Service power / for three-phase servomotors / rated value	2.2 kW	
Number of NC contacts / for auxiliary contact	1	
Number of NO contacts / for auxiliary contact	1	
Number of change-over switches / for auxiliary contact	0	
Type of assignement	2	
Type of protection	DMT 98 ATEX G 001	
Mechanical design:		
Design of the electrical connection / for main current circuit	Cage Clamp terminals	
Design of the electrical connection / for auxiliary and control current circuit	Cage Clamp terminals	
Size of the contactor / can be combined / company- specific	S00	

3RU1116-1GC1 Page 2

Type of fixing/fixation	stand-alone installation
Size of overload relay	S00
Ambient conditions:	
Protection class IP	IP20



last change: 10/31/2006

Technical Assistance:	Telephone:	+49 (0) 911-895-5900 (8°° - 17°° CET)
	Fax:	+49 (0) 911-895-5907
	E-Mail:	technical-assistance@siemens.com
	Internet:	www.siemens.de/lowvoltage/technical-assistance